Gemino - selection guide

Choose the Gemino rollator that suits you 100%





GEMINO 20

Light-weight design rollator. Great functionality at an attractive price



Indoor and outdoor use

Everyday use

150 kg 130 kg (M) 125 kg (S)



150-200 cm 135-170 cm (M) 125-165 cm (S) Also suitable for children



GEMINO30

Our original 100% rollator. Award-winning design combining high indoor maneuverability with outdoor performance. Lots of colour options and accessories for easy customization



Use indoors and out, mainly in the city

Everyday use 150 kg 130 kg (M) 125 kg (S)



150-200 cm 135-170 cm (M) 125-165 cm (S) Also suitable for children



Small turning radius for great indoor manoeuvrability



Easy personalization with frame colours and bag colours. Wide range of



GEMINO 60

Designed for any kind of terrain and heavy-duty use. Lightweight, yet rock-solid. All the benefits of the award-winning Gemino 30 and more



Mostly outdoor use, also on rugged terrain, occasionally indoors

Active / heavy-duty use



150 kg 150 kg (M)



150-200 cm 135-170 cm (M)

Extra wide and long

frame for ultimate

negotiation of any

stability

ohstacle



Extra-large and soft wheels ensure ultimate comfort and easy





GEMINO 30 walker

ILightweight walker with adjustable forearm supports. The perfect companion if you need extra support and stability indoors. Also great for gait training.



Everyday use / gait training



150 kg 130 kg (M)



150-200 cm 135-170 cm (M)



Height-adjustable forearm supports for extra support and



GEMINO 50 walker

Optimal support and stability indoors and out. Combines the comfortable rolling characteristics and stability of the Gemino 60 with the additional support and safety you'd expect from a walker.



Indoor and outdoor use, also on uneven terrain

Everyday use / gait training



130 kg 130 kg (M)



150-200 cm 135-170 cm (M)



Height-adjustable forearm supports for extra support and stability



Extra wide and long frame for ultimate stability



Extra-large and soft wheels ensure ultimate comfort and easy negotiation of any obstacle

Extra strong bag (10 kg load capacity)



GEMINO 30 SpeedControl

For extra secrurity the brakes in the rear wheels will automatically come into action in case of sudden acceleration. Great for gait training

mainly in the city

Everyday use

150-200 cm

135-170 cm (M)

125-165 cm (S)

Also suitable for children

Small turning radius

for great indoor

maneuverability

In case of sudden

acceleration, the

resistance

SpeedControl wheels

will automatically give

100 kg



GEMINO 30 parkinson

Specially designed for people with Parkinon's. Featuring a slowdown brake promoting a steady pace, and a reverse braking system and laser light to help with 'freezing'.



Use indoors and out, mainly in the city

Everyday use



130 kg 130 kg (M)



150-200 cm 135-170 cm (M)



Small turning radius for great indoor maneuverability



Reverse braking system: the rollator immediately stops moving once the brake is released



Slowdown break provides extra resistance and promotes a steady pace




Laser light can be activated to help overcome 'freezing'



Gemino range - specifications



















			_															
		GEMINO 20			GEMINO 30			GEMINO 50		GEMINO 30 walker		GEMINO 50 walker		Gen	GEMINO ZO SpeedControl		GEMINO 30 parkinson	
		20	20 M	205	30	30 M	305	60	60 M	30	30 M	60	60 M	30	30 M	305	30	30 M
DIMENSIONS																		
Maximum user weight	kg	150	130	125	150	130	125	150	150	150	130	130	130	100	100	100	130	130
Recommended user height	cm	150-200	135-170	125-165	150-200	135-170	125-165	150-200	135-170	150-200	135-170	150-200	135-170	150-200	135-170	125-165	150-200	135-170
Maximum load capacity in basket	kg	5	5	5	5	5	5	10	10	5	5	10	10	5	5	5	5	5
Total length (A)	cm	65	65	68	65	65	68	74	74	65	65	74	74	65	65	68	65	65
Total width B	cm	60	60	55	60	60	55	64	64	61	61	64	64	60	60	55	60	60
Total weight without basket (with basket)	kg	7.1 (7.3)	7.0 (7.2)	6.6 (6.8)	7.1 (7.4)	7.0 (7.3)	6.6 (6.8)	8.5 (8.8)	8.2 (8.5)	10.6 (10.9)	10.4 (10.7)	11.8 (12.1)	11.6 (11.9)	8.7 (8.9)	8.6 (8.8)	8.2 (8.4)	7.5 (7.8)	7.4 (7.7)
Width between centre of push handles ©	cm	47	47	42	47	47	42	51	51	25.5	25.5	32	32	47	47	42	47	47
Seat height D	cm	62	55	48	62	55	48	62	53	62	55	62	53	62	55	48	62	55
Total height (E)	cm	78 - 100	69 - 88	65 - 77	78 - 100	69 - 88	65 - 77	76-95	73 - 83	98 - 111.5	84 - 100	98.5 - 115.5	89.5 - 98.5	78 - 100	69 - 88	65 - 77	78 - 100	69 - 88
Total height folded	cm	80	76	69	80	76	69	84	80	97	89	109	101	80	76	69	80	76
Total lenght folded	cm	65	65	68	65	65	68	74	74	65	65	74	74	65	65	68	65	65
Total width folded	cm	23	23	23	23	23	23	23	23	35.5	35.5	35.5	35.5	23	23	23	23	23
Diameter front wheels F	cm	20 x 3.6	20 x 3.6	20 x 3.6	20 x 3.6	20 x 3.6	20 x 3.6	28 x 4.2	28 x 4.2	20 x 3.6	20 x 3.6	28 x 4.2	28 x 4.2	20 x 3.6	20 x 3.6	20 x 3.6	20 x 3.6	20 x 3.6
Diameter rear wheels 6	cm	20 x 3.6	20 x 3.6	20 x 3.6	20 x 3.6	20 x 3.6	20 x 3.6	23 x 4.2	23 x 4.2	20 x 3.6	20 x 3.6	23 x 4.2	23 x 4.2	20 x 3.6	20 x 3.6	20 x 3.6	20 x 3.6	20 x 3.6
PERFORMANCE																		
Turning radius	cm	84	84	79	84	84	79	95	95	84	84	95	95	84	84	79	84	84
COLOUR OPTIONS																		
Grey		\checkmark	√	\checkmark														
Silver grey					\checkmark	√	J	$\sqrt{}$	\checkmark	$\sqrt{}$	\checkmark	\checkmark	\checkmark	$\sqrt{}$	\checkmark	$\sqrt{}$	\checkmark	\checkmark
Champagne					\checkmark	$\sqrt{}$												
Midnight blue					\checkmark	√	√									$\sqrt{}$		
Pink					\checkmark		√									$\sqrt{}$		
Apple green					\checkmark	\checkmark												
Black					\checkmark													
CERTIFICATES																		
CE		\checkmark	$\sqrt{}$	$\sqrt{}$	\checkmark	\checkmark	$\sqrt{}$	\checkmark	$\sqrt{}$	$\sqrt{}$	$\sqrt{}$	$\sqrt{}$	$\sqrt{}$	$\sqrt{}$	$\sqrt{}$	$\sqrt{}$	\checkmark	$\sqrt{}$
EN 12182		\checkmark	√	\checkmark	\checkmark	\checkmark	√	√	\checkmark	$\sqrt{}$	\checkmark	\checkmark	\checkmark	$\sqrt{}$	√	$\sqrt{}$	\checkmark	$\sqrt{}$
ISO 11199-2		\checkmark	√	\checkmark	\checkmark	\checkmark	√	√	\checkmark					$\sqrt{}$	√	$\sqrt{}$	\checkmark	\checkmark
ISO 11199-3										1	√	√	√					



For further information on the full specification, options and accessories, please refer to the order form.

All information is subject to change without notification. Please consult Sunrise Medical with any queries you may have.

